

Compact Steam Trap Station

QuickStation...

QS10 Series

Save time, money and space





- Simple trap installation in minutes
- Compact, reliable all-in-one design
- Condensate drainage from steam mains, tracers and light processes

QuickStation makes steam trap installation simple, allowing you to focus on your process.



Built-in strainer and check valve

protect from scale and backflow
to improve production



Stainless steel construction is durable and corrosion-resistant for long service life



Universal connector enables horizontal and vertical installation

I Simple trap selection and installation

Steam traps can be installed in minutes, minimizing production downtime and with TLV's range of precision-engineered steam traps, allowing your process equipment to perform at optimal conditions.



I Flexible configuration for maximum reliability

QuickStation is available with single or double upstream/downstream isolation valves and multiple piping arrangements.

Each includes an integral strainer to help prevent equipment damage or production issues due to entrained material, and a check valve to prevent backflow.

Optional blowdown valve also available for inline scale removal to help further reduce maintenance and downtime.



QS10-B with optional BD2 blowdown valve



QS10-B with single upstream/downstream isolation valve



QuickStation





Specifications

QuickStation...

Model	QS10		
Connections	Screwed, SW, Flanged		
Valve Port	Full Bore		
Size (mm)	15, 20, 25		
PMO/PMA (MPaG)	10		
TMO/TMA (°C)	185		
No. of Valves	See datasheet		

PMA/TMA are pressure shell design conditions, **NOT** operating conditions.

Steam Trap Units*

Oteam hap onto							
Model	J32-X	S1(N)	S3	L21	P46UC		
Steam Trap Type	Free Float	Free Float	Free Float	Thermostatic	Thermodynamic		
PMO (MPaG)	3.2	2.1	2.1	2.1	4.6		
TMO (°C)	240	220	400	235	425		
Max. Discharge Capacity** (kg/h)	670	200	215	760	740		
Trap Image							

^{*} For more information, see the QuickTrap specifications data sheet for the steam trap employing the desired trap unit (trap unit - QuickTrap data sheet): J32-X; S1(N) - FS1(N); S3 - FS3; L21 - FL21/FL32; P46UC - FP46UC

^{**} Capacities shown here will vary depending on orifice numbers, type of X-element and/or pressure differential.



To avoid abnormal operation, accidents or serious injury, DO NOT use this product outside of the specification range Local regulations may restrict the use of this product to below the conditions quoted.

TLY: INTERNATIONAL, INC.

881 Nagasuna, Noguchi, Kakogawa, Hyogo 675-8511, JAPAN Tel: [81]-(0)79-427-1818 Fax: [81]-(0)79-425-1167 E-mail: tlv-japan@tlv.co.jp https://www.tlv.com

Manufacturer

TLV: CO., LTD.

Kakogawa, Japan

is approved by LRQA Ltd. to ISO 9001/14001

ISO 9001 ISO14001